
Small Tool Instruments and Data Management

# **M**itutoyo



# High-Accuracy Digimatic Micrometer MDH-25MB





# HIGH ACCURACY

World's First

μm\* Resolution
Digital Micrometer

High Accuracy MIEROMETE DIEIMATIE MIEROMETE

5mm 0.000

\*0.1 µm=0.0001 mm



### MDH-25MB

### Easy, Rapid and High-accuracy Measurement of Workpieces That Require an Accuracy of 1 µm or Less

Delivering a Maximum Permissible Error  $J_{\text{MPE}}$  of  $\pm 0.5$  µm accuracy at 0.1 µm resolution means Mitutoyo's MDH-25MB is the most accurate digital micrometer available\*, and this instrument will enable you to easily and rapidly measure workpieces that require very-high-accuracy measurement. This remarkable performance has been attained thanks to Mitutoyo's proprietary ABS (absolute) rotary encoder and high-accuracy thread cutting technology.

\*Mitutoyo's research as of July, 2018

#### Position and Merits of MDH-25MB



- Measuring accuracy equivalent to a laser micrometer
- No jig, etc. needed to be fabricated
- Simple measurement enabled even for very small parts
- Portable and compatible with standard workpiece measurement techniques, similar to conventional micrometers
- Economical low investment in equipment compared with other choices

## APPLICATION

# Beyond the Usual Micrometer! Many More Kinds of High-accuracy Parts Now Measurable.

This micrometer allows easy, rapid and high-accuracy measurement of workpieces that require a measuring accuracy of 1  $\mu$ m or less, such as medical parts, precision instruments and auto-parts regarded as difficult to be accurately measured with conventional micrometers.





Manufacturing

#### Pin gage measurement

Pin gages are widely used for measurement of the diameter or center-to-center distance of holes. The periodic calibration of a high-precision pin gage requires high-accuracy measure-







Medical care

#### Hypodermic needle measurement

To reduce injection pain as much as possible, the outside diameter of hypodermic needle tips has become much thinner. Some needles have a tip diameter of just 0.2 mm, thus requiring high-accuracy measurement.





Electric/electronic devices

#### Fiber optics measurement

The optical-transmission cylindrical "core" made of quartz glass is 0.01 to 0.05 mm in diameter. Since its thickness is similar to a strand of hair, high accuracy is required for its measurement.





Manufacturing

#### Gap gage calibration

Gap gages are widely used for easy measurement of small gaps in assemblies.

Periodic gage calibration is indispensable for accuracy control to detect undue wear.






Automobile and machine tools

#### Gear tooth measurement

As gears decrease in size and weight, the MDH allows for convenient high accuracy evaluation. MDH simply enables accuracy evaluation with it on hand for the customer demand of high accuracy.





Electric/electronic devices

#### Optical film measurement

Optical films are widely used to display still images or moving images on a car navigation device or LCD TV. The micrometer accuracy is a must for measuring film thickness.





Medical care

#### Implant measurement

An abutment is used for dental implants. Abutments have various lengths, angles, and materials. Each abutment needs to be made and measured very accurately.





Machine tools

#### Cutting tool measurement

The diameter of extremely small drills used for manufacturing precision tools and instruments requires high accuracy measurement.





Medical care

#### Catheter measurement

High-accuracy measurement is needed when manufacturing the fine tubing widely used in the medical field, such as a catheter that plays a crucial part in dilating a blood vessel.





Automobile/office equipment

#### Bearing measurement

High-accuracy measurement is required for the component parts of anti-friction ball and roller bearings that are required to support vibration-free rotation in high-quality products.

## TECHNOLOGY



#### Ratchet thimble with an anti-friction bearing

Measurement repeatability has been improved by changing from sliding to rolling friction to dramatically reduce the torque needed to operate the constant-force device. This makes measurement even more consistent, even for operators new to this micrometer.



### ABS (absolute) rotary encoder with a resolution of 0.1 µm and high-accuracy thread cutting technology


The development of a 5000-division rotary encoder has achieved the unprecedented resolution of 0.1  $\mu m$  in a hand-held micrometer.

The commercialization of this ABS (absolute) encoder has also improved its reliability. Additionally, since the spindle-thread pitch accuracy directly affects measuring accuracy, Mitutoyo has developed a series of technologies from thread cutting technology to thread evaluation technology, thereby guaranteeing the achievement of high accuracy.



#### Heat transfer reduction with a heat shield

The influence of heat transferred to the micrometer frame through hands has been reduced during measurement with this micrometer by fitting the supplied heat shield. The graph below shows that the heat shield almost eliminates thermally induced error by minimizing thermal expansion of the frame.



#### **■** Functions


- i di ictioni		
Preset (ABS measurement system):	The measurement origin can be preset to any value within the display range for convenience in measuring.	
Zero-setting (INC measurement system):	The display can be zeroed at any position of the spindle, making comparison measurement easier.  Returning to the absolute-measurement mode is easily accomplished.	
Hold:	The displayed value is held while the spindle is withdrawn and the micrometer moved so that the display can be read at the operator's convenience.	
Resolution switching:	The resolution of the display can be switched. If 0.1 $\mu$ m measurement is not required, the resolution can be switched to 0.5 $\mu$ m.	
Function lock:	Functions such as preset or zero-set can be locked to avoid inadvertently changing the origin position.	
On/off:	The power can be turned off after measurement is complete.  Even after the power is turned off, the origin or last zero-set position remains in the memory.	
Auto power off:	Even if the power is left on, the power turns off automatically if the micrometer is not used within a 20-minute period.	
Measurement data output:	Measurement data can be output, allowing easy incorporation of this instrument into a statistical process control or measurement system.	
Error alarm:	In the unlikely event of a display overflow or calculation error, an error message is displayed and measurement stops.  Measurement cannot continue until the error is corrected.  Also, if the battery voltage drops below a certain point, the battery indicator will turn on before measurement becomes impossible, warning the user that the battery needs to be replaced.	

#### **■** Specifications

•				
	Metric	Inch/Metric		
Order No.	293-100-10	293-130-10		
Measuring range	0 – 25 mm	0 – 1 in		
Resolution	0.0001 mm/0.0005 mm (switchable)	0.000005 in/0.00002 in 0.0001 mm/0.0005 mm (switchable)		
Maximum permissible error JMPE	±0.5 μm	±0.00002 in		
J MPE	0.3 μm/0.6 μm	0.000012 in/0.000024 in		
Measuring surface	ø3.2 mm			
Measuring force	7 to 9 N			
Measuring system	Electromagnetic induction type ABS rotary sensor			
Mass	400 g (440 g with heat shield attached)			
Power supply	Lithium battery (CR2032) x 1			
Battery life	Approx. two years when used under normal conditions			

#### ■ Dimensions

Unit (mm)



## USABILITY



Reliable operation

The sound of the ratchet provides a reliable operation and repeatable measurements.

#### Absolute encoder

The ABS (absolute) rotary encoder eliminates the need for origin point setting at every power-on, allowing immediate starting of

This encoder achieves high reliability without causing an overspeed error.





Wear-resistant carbide tip

The ø3.2 mm carbide tip on the measuring face is highly resistant to wear, allowing accurate measurement for an extended period

#### Zero-setting function

This function allows the displayed to be zero set at any position, thus facilitating comparative measurement. Also the absolute value from the origin can be restored.



Versatile functionality enhances productivity and ease of use

This micrometer is equipped with many useful and time-saving functions such as resolution switching (0.0001 mm/0.0005 mm), function lock, and presetting.

#### Built-in "Hold" function

This function can hold (freeze) the displayed value. Enables the micrometer to be removed from a workpiece when the readout is not easily viewable so that the measurement value can be read at your convenience.

#### ■ Measurement Data Recording Tools (Optional)



Mini-printer equipped with data logger function Digimatic mini processor DP-1VA LOGGER No. 264-505 (See Catalog No. E12041)

The data logger function allows data output to a PC and automatic logging of measurement data in an Excel-format inspection certificate using Mitutoyo USB-ITPAK. It provides significant potential for efficiency improvement in the QC function.


#### Standard accessories

- Heat shield (04AAB969A: 293-100-10 04AAB969B: 293-130-10) x 1
- Lithium battery (CR2032: Battery supplied is for testing purpose only) x 1
  • Spanner (200877) x 1
- Screwdriver (04AAB985) x 1
- Lens paper
- Inspection certificate

#### Optional accessories


• Lens paper x 1,000 (04AZB581)

• Wired Connection to PC via USB Input Tool Series (Refer to Catalog E12007)



Connecting cables specific to outputfunction equipped models

A 1 m: 05CZA662 2 m: 05CZA663



B For standard use (160 mm): 02AZD790B For foot switch use: 02AZE140B



U-WAVE-R: 02AZD810D



Whatever your challenges are, Mitutoyo supports you from start to finish.

Mitutoyo is not only a manufacturer of top quality measuring products but one that also offers qualified support for the lifetime of the equipment, backed up by comprehensive services that ensure your staff can make the very best use of the investment.

Apart from the basics of calibration and repair, Mitutoyo offers product and metrology training, as well as IT support for the sophisticated software used in modern measuring technology. We can also design, build, test and deliver bespoke measuring solutions and even, if deemed cost-effective, take your critical measurement challenges in-house on a sub-contract basis.

Note: Product illustrations are without obligation. Product descriptions, in particular any and all technical specifications, are only binding when explicitly agreed upon.

MITUTOYO and MiCAT are either registered trademarks or trademarks of Mitutoyo Corp. in Japan and/or other countries/regions. Other product, company and brand names mentioned herein are for identification purposes only and may be the trademarks of their respective holders.



www.mitutoyo.com.sg | www.mitutoyo.com.my www.mitutoyo.co.th | www.mitutoyo.co.id www.mitutoyo.com.vn | www.mitutoyo.com.ph

Small Tools Authorized Distributor

### **M**itutoyo

#### Mitutoyo Asia Pacific Pte. Ltd.

Company Reg No. 197800892N

24 Kallang Avenue, Mitutoyo Building, Singapore 339415

Tel: (65) 6294 2211 Fax: (65) 6299 6666 E-mail: mapsq@mitutoyo.com.sq

#### Mitutovo (Malaysia) Sdn. Bhd.

Mah Sing Integrated Industrial Park, 4, Jalan Utarid U5/14, Section U5, 40150 Shah Alam, Selangor, Malaysia Tel: (60) 3-7845 9318

Fax: (60) 3-7845 9346 E-mail: mmsb@mitutovo.com.mv

Penang Branch Tel: (60) 4-641 1998 Fax: (60) 4-641 2998

Johor Branch Tel: (60) 7-352 1626 Fax: (60) 7-352 1628

#### Mitutoyo (Thailand) Co., Ltd.

76/3-5, Chaengwattana Road, Kwaeng Anusaowaree, Khet Bangkaen, Bangkok 10220 Thailand Tel: (66) 2080 3500 Fax: (66) 2521 6136 E-mail: office@mitutoyo.co.th Chonburi Branch Tel: (66) 2080 3563 Fax: (66) 3834 5788 ACC Branch

Tel: (66) 2080 3565

#### PT. Mitutovo Indonesia

Jalan Sriwijaya No.26 Desa cibatu Kec. Cikarang Selatan Kab. Bekasi 17530, Indonesia Tel: (62) 21-2962 8600 Fax: (62) 21-2962 8604 E-mail: ptmi@mitutoyo.co.id

#### Mitutoyo Vietnam Co., Ltd. 1st & 2nd Floor, MHDI Building, No. 60 Hoang Quoc Viet Road,

Nghia Do Ward. Cau Giav District. Hanoi, Vietnam Tel: (84) 24-3768 8963 Fax: (84) 24-3768 8960 E-mail: mvc@mitutoyo.com.vn Ho Chi Minh City Branch Tel: (84) 28-3840 3489 Fax: (84) 28-3840 3498 Hai Phong City Branch Tel: (84)22-5398 9909

#### Mitutoyo Philippines, Inc. Unit 1B & 2B LTI

Administration Building 1, Annex 1, North Main Avenue, Laguna Technopark, Biñan, Laguna 4024, Philippines Tel: (63) 49-544 0272 Fax: (63) 49-544 0272 E-mail: mpi@mitutoyo.com.ph

MAP • 1414(1) Printed in Singapore 0.560321(0.2)TM